

BASETECH

POO080X34-Ø12

EAN 4031582418972



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Load capacity Static	551.16 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.14 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.34 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Hardness of tread (D)	65 Shore D

BASETECH

POO080X34-Ø12

EAN 4031582418972



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

