

PRODUCT INFORMATION

ELASTECH

IEP 125x50-Ø25 HL60

EAN 4031582319699



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Load capacity at 3.7 mph	529.11 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.97 lb

ELASTECH


IEP 125x50-Ø25 HL60

EAN 4031582319699

Order number 00829687
Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

ELASTECH

IEP 125x50-Ø25 H1.60

EAN 4031582319699

Order number 00840637



BETTER MOBILITY. BETTER LIFE.