

# FOOTMASTER

FOOT MASTER GD- 40-S-NYN

EAN 4031582413199



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ○ ○ ○ ○ ○ |
| Movement Noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion Resistance | ○ ○ ○ ○ ○ |

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product Name                | Footmaster    |
| Type                        | Swivel castor |
| Load capacity at 3 km/h     | 60 kg         |
| Electric Conductive         | No            |
| Stainless                   | No            |
| Load capacity Static        | 60 kg         |
| Temperature range (Minimum) | -10 °C        |
| Temperature range (Maximum) | 90 °C         |
| Overall Height              | 71 mm         |
| Overall width               | 58 mm         |
| Overall weight              | 0.32 kg       |

## HOUSING

|                     |        |
|---------------------|--------|
| Housing Color       | White  |
| Offset              | 30 mm  |
| Swivel radius       | 51 mm  |
| Swivel interference | 102 mm |
| Dome diameter       | 58 mm  |

## WHEEL

|             |                        |
|-------------|------------------------|
| Bearing     | Roller bearing, damped |
| Wheel Color | Black                  |
| Diameter    | 42 mm                  |
| Tread width | 19 mm                  |
| Body width  | 19 mm                  |

# FOOTMASTER

FOOT MASTER GD- 40-S-NYN

EAN 4031582413199

Order number 00062067  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

