

PRODUCT INFORMATION

NOVATECH

ITP125x50-Ø20-SH80A flat

EAN 4031582428612



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	881.85 lb
Load capacity at 3.7 mph	705.48 lb
Electric conductive	no
Stainless	no
Load capacity Static	1763.7 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.77 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Tread profile	flat
Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Hardness of tread (A)	80 Shore A

NOVATECH


ITP125x50-Ø20-SH80A flat

EAN 4031582428612



BETTER MOBILITY. BETTER LIFE.


Product Drawings



NOVATECH

ITP125x50-Ø20-SH80A flat

EAN 4031582428612



BETTER MOBILITY. BETTER LIFE.