PRODUCT INFORMATION

PURETECH

PVR 100x35-Ø12

EAN 4031582321258



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Roller bearing
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	35 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	75 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.23 kg

© Copyright 2026 TENTE International GmbH


PURETECH

PVR 100x35-Ø12

EAN 4031582321258

Order number 00004952

Product Drawings



© Copyright 2026 TENTE International GmbH