

# ALPHA STAINLESS

8470UFC125P30-13

EAN 4031582422412



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha stainless               |
| Type                        | Swivel castor                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 150 kg                        |
| Stainless                   | ✓                             |
| Load capacity Static        | 300 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall height              | 155 mm                        |
| Overall weight              | 0.975 kg                      |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Polyamide                             |
| Tread hardness        | soft                                  |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing, stainless     |
| Axle                  | Screwed with nut                      |
| Threadguards          | With threadguard                      |
| Diameter              | 125 mm                                |
| Tread width           | 40 mm                                 |
| Hardness of tread (A) | 64 Shore A                            |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Stainless steel, heavy |
| Fork shape          | Broad                  |
| Swivel bearing      | Two ball races         |
| Offset              | 40 mm                  |
| Swivel radius       | 102.5 mm               |
| Swivel interference | 205 mm                 |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 13 mm     |

# ALPHA STAINLESS

8470UFC125P30-13

EAN 4031582422412



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

