

LINEA CLINIC LOAD

5986UAP150R36-32S30

EAN 4031582382525
Order number 00038829



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|----------------------------------------|
| Product name | Linea clinic load |
| Housing type | Swivel castor with central, total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 200 kg |
| Load capacity Static | 400 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 155 mm |
| Overall width | 71 mm |
| Overall weight | 1.506 kg |

WHEEL

| | |
|----------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 15 mm |

HOUSING

| | |
|---------------------|-----------------------------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Two ball races, reinforced or stainless |
| Offset | 47.5 mm |
| Swivel radius | 122.5 mm |
| Swivel interference | 254 mm |

FITTING

| | |
|---------------|----------------------------------------------------|
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm |
| Bolt length | 50 mm |

