

PURETECH

DRR125x37-Ø12

EAN 4031582410822



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.58 kg

WHEEL

Body material	Sheet Steel
Tread Material Mix	Wound tread made of canvas and phenolic resin
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Hardness of tread (A)	85 Shore A

