

## ZETA

4680FTP160P63 TFR

EAN 4031582386240



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Zeta                          |
| Type                        | Swivel caster                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 1763.7 lb                     |
| Load capacity at 3.7 mph    | 1410.96 lb                    |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 3527.39 lb                    |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 7.87 in                       |
| Overall weight              | 11.82 lb                      |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Housing Material    | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Housing Color       | Blue passivated                         |
| Offset              | 2.17 in                                 |
| Swivel radius       | 5.31 in                                 |
| Swivel interference | 10.63 in                                |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Casting                |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Threadguards          | With threadguard       |
| Diameter              | 6.3 in                 |
| Tread width           | 1.97 in                |
| Hardness of tread (A) | 92 Shore A             |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.39 in           |
| Plate width                 | 4.13 in           |
| Plate hole length (Maximum) | 4.13 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 3.15 in           |
| Plate hole diameter         | 0.43 in           |

# ZETA

4680FTP160P63 TFR

EAN 4031582386240



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

