

ALPHA

3478UFJ100P62 TYRE-5015

EAN 4031582377804
Order number 00032315



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha |
| Housing type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 160 kg |
| Load capacity Static | 320 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 128 mm |
| Overall width | 85 mm |
| Overall weight | 0.514 kg |

WHEEL

| | |
|-----------------------|---------------------------------------|
| Body material | Polyamide |
| Tread material | Elastic tire, non-marking, vulcanized |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Tread color | Sky blue (RAL5015) |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 34 mm |
| Body width | 34 mm |
| Hardness of tread (A) | 63 Shore A |

HOUSING

| | |
|---------------|--------------------|
| Material fork | Steel sheet, heavy |
| Fork shape | Broad |
| Colour | Blue passivated |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 103 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

ALPHA

3478UFJ100P62 TYRE-5015

EAN 4031582377804
Order number 00032315



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

