

SUPRATECH

PJR200X40-Ø20 HL58

EAN 4031582442519



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 7.87 in |
| Tread width | 1.57 in |
| Axle hole diameter | 0.79 in |
| Hub length | 2.28 in |
| Hardness of tread (A) | 87 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Supratech |
| Housing type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 352.74 lb |
| Load capacity Static | 705.48 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 1.58 lb |

SUPRATECH

PJR200X40-Ø20 HL58

EAN 4031582442519



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

