

DURATECH

TOP082X100-Ø20

EAN 4031582452402



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	82 mm
Tread width	100 mm
Axle hole diameter	20 mm
Hub length	102 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Load capacity at 3 km/h	900 kg
Load capacity Static	1800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.61 kg

DURATECH

TOP082X100-Ø20

EAN 4031582452402



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

