

MAXTECH

PNP200X45-Ø8 MS

EAN 4031582320640



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	45 mm
Axle hole diameter	8 mm
Hub length	53 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.555 kg

MAXTECH

PNP200X45-Ø8 MS

EAN 4031582320640



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

