

ZETA

4688ICP200P63

EAN 4031582451863



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity at 6 km/h	640 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	240 mm
Overall weight	2.652 kg

WHEEL

Body material	Aluminium
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	117 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA

4688ICP200P63

EAN 4031582451863



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

