PRODUCT INFORMATION

DURATECH

MOP 125x50-Ø20

EAN 4031582320015



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6304

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	4497.42 lb
Load capacity at 3.7 mph	3747.85 lb
Electric conductive	no
Stainless	no
Load capacity Static	7495.71 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	2.14 lb

© Copyright 2026 TENTE International GmbH


DURATECH

MOP 125x50-Ø20

EAN 4031582320015

Order number 00801259

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

MOP 125x50-Ø20

EAN 4031582320015

Order number 00801259



© Copyright 2026 TENTE International GmbH