

BASETECH

POO3X1.25-Ø0.5 HL 40

EAN 4031582436082



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3 in
Tread width	1.25 in
Axle hole diameter	0.48 in
Hub length	1.57 in
Hardness of tread (D)	66 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	253.53 lb
Load capacity Static	507.06 lb

BASETECH

POO3X1.25-Ø0.5 HL 40

EAN 4031582436082



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

