

## ELASTECH

SFP 200x50-Ø20 HL60 plus

EAN 4031582322217



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOČAK

|                            |                                            |
|----------------------------|--------------------------------------------|
| Tread hardness             | mekan                                      |
| Materijal za telo          | Čelik od limova, težak                     |
| materijal omotaca          | Elastična guma, neobeležena, vulkanizovana |
| Nošenje                    | precizini kuglični lezaj                   |
| Boja Tocak                 | Siva/ne-označavanje                        |
| stitnici omotaca           | Sa threadguard                             |
| Prečnik                    | 200 mm                                     |
| Širina omotac              | 50 mm                                      |
| dimenzija rupa osovina     | 20 mm                                      |
| duzina glavine             | 60 mm                                      |
| Širina tela                | 50 mm                                      |
| Teškoća gazećeg omotac (A) | 68 Šešelj A                                |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ● |
| Buka u pokretu         | ● ● ● ● ● |
| Ishrana                | ● ● ● ● ● |
| otpornost na rdju      | ● ● ● ● ● |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Elastech                     |
| Tip                            | Tocak                        |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 600 kg                       |
| Nosivost na 6 km/h             | 500 kg                       |
| Električni provod              | no                           |
| nerdjajući                     | no                           |
| Statički Nosivost              | 1000 kg                      |
| Temperaturni opseg (Minimalno) | -20 °C                       |
| Opseg temperature (maksimalni) | 85 °C                        |
| Ukupna težina                  | 3.48 kg                      |

# ELASTECH


SFP 200x50-Ø20 HL60 plus

EAN 4031582322217

Broj porudžbine 00830559  
Product Drawings



BETTER MOBILITY. BETTER LIFE.




# ELASTECH

SFP 200x50-Ø40 HL60 plus

EAN 4031582322117

Broj porudžbine 0084559



BETTER MOBILITY. BETTER LIFE.