

ELASTECH

SFP 200x50-Ø20 HL60 plus

EAN 4031582322217



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Čelik od limova, težak
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglični lezaj
Boja Tocak	Siva/ne-označavanje
štitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavčine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	500 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	3.48 kg

ELASTECH


SFP 200x50-Ø20 HL60 plus

EAN 4031582322217

Broj porudžbine 00830559
Product Drawings



BETTER MOBILITY. BETTER LIFE.




ELASTECH

SFP 200x50-Ø40 HL60 plus

EAN 4031582322117

Broj porudžbine 0084559



BETTER MOBILITY. BETTER LIFE.