

NOVATECH

ITP 125x50-Ø20 soft cv

EAN 4031582329483



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Tread profile	konveksan
Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglični lezaj
Boja Tocak	Saobraćajna siva A (RAL7042)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	400 kg
Nosivost na 6 km/h	320 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	800 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.89 kg




NOVATECH

ITP 125x50-Ø20,5 soft ey

EAN 4031582329483

Broj porudžbine 008311428



BETTER MOBILITY. BETTER LIFE.