

# AGILA

2470DYK100R05-28

EAN 4031582340525



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 80 kg                     |
| Electric conductive         | ✓                         |
| Load capacity Static        | 160 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 85 °C                     |
| Overall height              | 138 mm                    |
| Overall weight              | 1.105 kg                  |

### WHEEL

|                       |                                          |
|-----------------------|------------------------------------------|
| Body material         | Sheet Steel                              |
| Tread material        | Solid rubber, black, electric-conductive |
| Bearing               | Cone ball bearing                        |
| Threadguards          | With threadguard                         |
| Diameter              | 100 mm                                   |
| Tread width           | 32 mm                                    |
| Hardness of tread (A) | 80 Shore A                               |

### HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 38 mm               |
| Swivel radius       | 88 mm               |
| Swivel interference | 176 mm              |

### FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 28 mm             |
| Bolt length   | 45 mm             |

# AGILA

2470DYK100R05-28

EAN 4031582340525



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

