

# SOCKET

R40-18x18 / 11

EAN 4031582090178



BETTER MOBILITY. BETTER LIFE.



图片可能与原产品不同

## 表现

耐腐蚀性



## 核心属性

|           |         |
|-----------|---------|
| 产品名称      | 插座      |
| 外壳类型      | 附件      |
| 3 km/h的载重 | 40 kg   |
| 导电        | 否       |
| 不锈        | 否       |
| 静态载重      | 80 kg   |
| 总高        | 36 mm   |
| 总重量       | 0.01 kg |

## 固定件

|       |         |
|-------|---------|
| 固定件类型 | 合成插座，方形 |
| 螺栓直径  | 18 mm   |

# SOCKET

R40-18x18 / 11


EAN 4031582090178

订单号 00009044

产品图纸



BETTER MOBILITY. BETTER LIFE.



| Bezeichnung | A  | B    | C  |
|-------------|----|------|----|
| R40-16x16   | 16 | 20   | 36 |
| R40-17x17   | 17 | 19   | 36 |
| R40-18x18   | 18 | 20   | 36 |
| R40-21x21   | 21 | 23,5 | 36 |
| R40-22x22   | 22 | 24,5 | 36 |
| R40-23x23   | 23 | 25,5 | 36 |
| R40-26x26   | 26 | 30   | 36 |