

BASETECH

POR 108X36-Ø12 HL44,4

EAN 4031582320794
Order number 00030953



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Roller bearing |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 4.25 in |
| Tread width | 1.42 in |
| Axle hole diameter | 0.47 in |
| Hub length | 1.75 in |
| Body width | 1.42 in |
| Hardness of tread (D) | 65 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Basetech |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 352.74 lb |
| Load capacity Static | 705.48 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 0.34 lb |

BASETECH

POR 108X36-Ø12 HL44,4

EAN 4031582320794
Order number 00030953



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

