

STEM

B10-10X20 / 10

EAN 4031582438048



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ●●●○○

CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	132.28 lb
Load capacity Static	264.55 lb
Overall height	0.18 in
Overall weight	0.08 lb

WHEEL

Axle	Riveted
------	---------

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.39 in