

PURETECH AIR

DQP400X100-Ø20 HL74 4PR

EAN 4031582318029



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Pneumatic tyre, block profile
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	400 mm
Tread width	100 mm
Axle hole diameter	20 mm
Hub length	74 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Housing type	Wheel
Load capacity at 3 km/h	200 kg
Load capacity Static	400 kg
Overall weight	2.665 kg

PURETECH AIR

DQP400X100-Ø20 HL74 4PR

EAN 4031582318029



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

