PRODUCT INFORMATION

KAPPA LOAD

9651FTP300P64 CL97

EAN 4031582314557



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Kappa load
Type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2400 kg
Load capacity at 6 km/h	2000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	4000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall Height	355 mm
Overall width	140 mm
Overall weight	21.52 kg

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel Bearing	Deep-groove ball thrust roller bearing
Housing Color	Zink-iron (transparent)
Offset	76 mm
Swivel radius	230 mm
Swivel interference	460 mm
Lubrication nipple	1
Dome diameter	140 mm

WHEEL

Body material	Cast iron
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	300 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Large rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Maximum)	140 mm
Plate hole diameter	15 mm

© Copyright 2026 TENTE International GmbH


KAPPA LOAD


9651FTP300P64 CL97


EAN 4031582314557

Order number 00863069

Product Drawings







© Copyright 2026 TENTE International GmbH