

ALPHA STAINLESS

8470PIO080P30-13

EAN 4031582381573



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 70 kg |
| Stainless | ✓ |
| Load capacity Static | 140 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 108 mm |
| Overall weight | 0.719 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 80 mm |
| Tread width | 35 mm |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 44.5 mm |
| Swivel radius | 84.5 mm |
| Swivel interference | 169 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |

ALPHA STAINLESS

8470PIO080P30-13

EAN 4031582381573



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

