


# NOVATECH

ETY 080X25-Ø25

EAN 4031582369427  
Broj porudžbine 00839178

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj (RS/2RS)
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	80 mm
Širina omotac	25 mm
dimenzija rupa osovina	25 mm
dužina glavčine	12 mm
Širina tela	25 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Nosivost na 6 km/h	130 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,38 kg

# NOVATECH

ETY 080X25-Ø25

EAN 4031582369427  
Broj porudžbine 00839178



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

