

DURATECH

TOP 085X95-Ø20 HL97

EAN 4031582334234
Order number 00839855



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.35 in
Tread width	3.74 in
Axle hole diameter	0.79 in
Hub length	3.82 in
Body width	3.74 in
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1984.16 lb
Load capacity at 3.7 mph	1587.33 lb
Load capacity Static	3968.32 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.25 lb

DURATECH

TOP 085X95-Ø20 HL97

EAN 4031582334234
Order number 00839855



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

