

AGILA US

2675PJO5X1.25P30-13

EAN 4031582435832



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila US
Housing type	Swivel castor with wheel brake
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	125 kg
Load capacity Static	250 kg
Overall height	155 mm

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	127 mm
Tread width	31.75 mm
Axle hole diameter	10 mm
Hardness of tread (A)	77 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	37 mm
Swivel radius	118.5 mm
Swivel interference	237 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm