

AGILA

R47-Ø36-40 INOX_TBE

EAN 4031582437911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Accessory
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall weight	0.39 lb

HOUSING

Stainless	✓
-----------	---

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	1.42 in
Expander fitting (Maximum)	1.57 in
Hint	Please indicate required tube innerdiameter when ordering.