

## P41-38X38 / 10 DRILLED PLATE

EAN 4031582411928



Image may differ from the original product

### PERFORMANCE

Corrosion resistance ● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Overall height	10 mm
Overall weight	0.053 kg

### FITTING

Fitting type	Square plate
Plate length	38 mm
Plate width	38 mm
Plate hole length (Maximum)	27 mm
Plate hole width (Maximum)	27 mm
Plate hole diameter	5 mm