

LINEA LOW HEIGHT

5940UAP075P30-10 LH 9002/7015/9002

EAN 4031582370768



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea low height
CO2 emission (scope 3)	1.18
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	198.42 lb
Electric conductive	no
Stainless	no
Load capacity Static	396.83 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.07 in
Overall width	2.28 in
Overall weight	0.47 lb

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Housing Color	Gray white (RAL9002)
Offset	0.91 in
Swivel radius	2.38 in
Swivel interference	4.76 in
Dome diameter	1.18 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Tread color	Slate gray (RAL7015)
Wheel color	Slate gray (RAL7015)
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.59 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.59 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.39 in

LINEA LOW HEIGHT

5940UAP075P30-10 LH 9002/7015/9002


EAN 4031582370768

Order number 00770588

Product Drawings



BETTER MOBILITY. BETTER LIFE.



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award