

AGILA

R07-Ø36-39 INOX_TBE

EAN 4031582437867



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Accessory
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall weight	0.144 kg

HOUSING

Stainless	✓
-----------	---

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	36 mm
Expander fitting (Maximum)	39 mm
Hint	Please indicate required tube innerdiameter when ordering.