

# ZETA

4680FTP200P63 TFR

EAN 4031582386257



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Zeta                          |
| Type                        | Swivel castor                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 800 kg                        |
| Load capacity at 6 km/h     | 640 kg                        |
| Load capacity Static        | 1600 kg                       |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 240 mm                        |
| Overall weight              | 6.503 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Cast iron              |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Threadguards          | With threadguard       |
| Diameter              | 200 mm                 |
| Tread width           | 50 mm                  |
| Hardness of tread (A) | 92 Shore A             |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Material fork       | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Offset              | 55 mm                                   |
| Swivel radius       | 155 mm                                  |
| Swivel interference | 310 mm                                  |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 105 mm                   |
| Plate hole length (Maximum) | 105 mm                   |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 80 mm                    |
| Plate hole diameter         | 11 mm                    |

# ZETA

4680FTP200P63 TFR

EAN 4031582386257



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

