

# SUPRATECH

PJP125X32-Ø8,3 2.0

EAN 4031582070  
Order number 10010291



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	8 mm
Hub length	36.5 mm
Hardness of tread (A)	85 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
CO2 emission (scope 3)	0.99 kg CO2e
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.237 kg

# SUPRATECH

PJP125X32-Ø8,3 2.0

EAN 4031582070  
Order number 10010291



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

