

DURATECH

TOP 080X60-Ø20 HL60

EAN 4031582365436
Order number 00860864



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 3.15 in |
| Tread width | 2.36 in |
| Axle hole diameter | 0.79 in |
| Hub length | 2.36 in |
| Body width | 2.36 in |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6204 |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Duratech |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 1322.77 lb |
| Load capacity at 3.7 mph | 1102.31 lb |
| Load capacity Static | 2204.62 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 0.96 lb |

DURATECH

TOP 080X60-Ø20 HL60

EAN 4031582365436
Order number 00860864



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

