

SUPRATECH

PJO160X40-Ø20 HL58

EAN 4031582442472



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	440.92 lb
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.95 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (A)	87 Shore A

SUPRATECH

PJO160X40-Ø20 HL58

EAN 4031582442472



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

