

NOVATECH

ETP080X30-Ø12 HL28_TBE

EAN 4031582438055



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	1.18 in
Axle hole diameter	0.47 in
Hub length	1.1 in
Hardness of tread (A)	92 Shore A
Bearing type	6201

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 1.8 mph	396.83 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.09 lb

TECHNICAL DRAWINGS

