PRODUCT INFORMATION

# ALPHA STAINLESS

8477IDG100P62

EAN 4031582433012



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●●● |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Alpha stainless |
| Type | Swivel caster with total lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 176.37 lb |
| Electric conductive | no |
| Stainless | Yes |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | -22 °F |
| Temperature range (Maximum) | 482 °F |
| Overall height | 5.04 in |
| Overall weight | 1.81 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Housing Color | Stainless steel |
| Offset | 1.61 in |
| Swivel radius | 3.58 in |
| Swivel interference | 7.17 in |

## WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Aluminum |
| Tread material | Damping, heat resistant |
| Bearing | Dry bearing bush |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.38 in |
| Hardness of tread (A) | 75 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 4.13 in |
| Plate width | 3.35 in |
| Plate hole length (Minimum) | 3.03 in |
| Plate hole length (Maximum) | 3.15 in |
| Plate hole width (Maximum) | 2.36 in |
| Plate hole diameter | 0.35 in |

© Copyright 2026 TENTE International GmbH


# ALPHA STAINLESS


8477IDG100P62


EAN 4031582433012


BETTER MOBILITY. BETTER LIFE.

## Product Drawings






© Copyright 2026 TENTE International GmbH