PRODUCT INFORMATION

ALPHA STAINLESS

8478XSC100P62

EAN 4031582381740

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Fixed caster
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Electric conductive	Yes
Stainless	Yes
Load capacity Static	705.48 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	5.04 in
Overall width	3.35 in
Overall weight	1.19 lb

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Housing Color	Stainless steel

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Wheel color	Silver gray (similar RAL7001)
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.34 in
Body width	1.34 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	3.94 in
Plate width	3.35 in
Plate hole length (Minimum)	3.03 in
Plate hole length (Maximum)	2.36 in
Plate hole width (Minimum)	3.03 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.35 in

© Copyright 2026 TENTE International GmbH


ALPHA STAINLESS


8478XSC100P62


EAN 4031582381740

Order number 00035828

Product Drawings







© Copyright 2026 TENTE International GmbH