

FOOTMASTER

FOOT MASTER GDR- 60-F-NYN

EAN 4031582413298



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	250 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	82.5 mm
Ukupna širina	70 mm
Ukupna težina	0.7 kg

KUCISTE

Boja	Beli
offset	38 mm
okretni radijus	63 mm
Otpor okretanju	126 mm
Prečnik kupole	70 mm

TOCAK

Nošenje	kotrljajuci lezaj, navlažen
Boja Tocak	Crna
Prečnik	50 mm
Širina omotac	25 mm
Širina tela	25 mm

PRILAGOĐAVANJE

Dužina ploče	73 mm
Širina ploče	73 mm
Dužina otvora ploče (maksimalna)	58 mm
Širina otvora ploče (maksimalna)	58 mm
Prečnik otvora ploče	7 mm

FOOTMASTER

FOOT MASTER GDR- 60-F-NYN

EAN 4031582413298

Broj porudžbine 00062080
Product Drawings



BETTER MOBILITY. BETTER LIFE.

