

# ZETA

4688IEP160P63

EAN 4031582308266



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ● ● |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Zeta                          |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 350 kg                        |
| Load capacity at 6 km/h     | 280 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 700 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 85 °C                         |
| Overall Height              | 200 mm                        |
| Overall width               | 117 mm                        |
| Overall weight              | 2.57 kg                       |

### HOUSING

|                  |                         |
|------------------|-------------------------|
| Housing Material | Steel sheet, very heavy |
| Fork shape       | Broad, reinforced       |
| Housing Color    | Blue passivated         |

### WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Tread hardness        | soft                            |
| Body material         | Aluminium                       |
| Tread Material Mix    | Elastic tire, black, vulcanized |
| Bearing               | Precision ball bearing          |
| Axle                  | Screwed with nut                |
| Wheel Color           | Jet black (similar RAL9005)     |
| Threadguards          | Without threadguard             |
| Diameter              | 160 mm                          |
| Tread width           | 50 mm                           |
| Body width            | 50 mm                           |
| Hardness of tread (A) | 67 Shore A                      |

### FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 117 mm                   |
| Plate hole length (Minimum) | 75 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# ZETA

4688IEP160P63

EAN 4031582308266

Order number 00804233

Product Drawings



BETTER MOBILITY. BETTER LIFE.

