

AGILA CARE US

2444UAP200R36-32S

EAN 4031582387452



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila care US
Type	Swivel caster with central, total or directional lock
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 1.8 mph	330.69 lb
Load capacity at 2.5 mph	330.69 lb
Electric conductive	no
Stainless	no
Load capacity Static	661.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	9.45 in

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Precision ball bearing
Housing Color	Blue passivated
Offset	2.44 in
Swivel radius	6.38 in
Swivel interference	12.76 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.26 in
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	1.42 in
Bolt length	1.26 in