

# ELASTECH

UFC100X34@08X45

EAN 4031582422269



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.34 in
Axle hole diameter	0.31 in
Hub length	1.77 in
Hardness of tread (A)	64 Shore A

## HOUSING

Stainless	✓
-----------	---

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.67 lb

# ELASTECH

UFC100X34@08X45

EAN 4031582422269



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

