

# NOVATECH

ITP 100X40-Ø15 HL40

EAN 4031582324525

Broj porudžbine 00830926



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	40 mm
dimenzija rupa osovina	15 mm
dužina glavcine	40 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Nosivost na 6 km/h	240 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,576 kg

# NOVATECH

ITP 100X40-Ø15 HL40

EAN 4031582324525

Broj porudžbine 00830926



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

