

PRODUCT INFORMATION

DURATECH HEAT

IOG 100x35-Ø8,4 clip

EAN 4031582347234



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.34 kg

WHEEL

Body material	Aluminium
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Wheel Color	Metallic
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle Hole Diameter	8.4 mm
Hub Length	45 mm
Body width	35 mm
Hardness of tread (D)	95 Shore D

DURATECH HEAT

IOG 100x35-Ø8,4 clip

EAN 4031582347234

Order number 00034267
Product Drawings



BETTER MOBILITY. BETTER LIFE.

