

AGILA

2470DYK075R07-Ø24-27

EAN 4031582340747



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement Noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product Name | Agila |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 55 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 110 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 103 mm |

HOUSING

| | |
|---------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 24 mm |
| Swivel radius | 61.5 mm |
| Swivel interference | 123 mm |

WHEEL

| | |
|-----------------------|--|
| Body material | Sheet Steel |
| Tread Material Mix | Solid rubber, black, electric-conductive |
| Bearing | Cone ball bearing |
| Threadguards | With threadguard |
| Diameter | 75 mm |
| Tread width | 25 mm |
| Hardness of tread (A) | 80 Shore A |

FITTING

| | |
|----------------------------|--|
| Fitting type | Synthetic expander, round |
| Expander fitting (Minimum) | 24 mm |
| Expander fitting (Maximum) | 27 mm |
| Hint | Please indicate required tube innerdiameter when ordering. |

AGILA

2470DYK075R07-Ø24-27

EAN 4031582340747



BETTER MOBILITY. BETTER LIFE.

Product Drawings

