

# ALPHA

3477UFJ125P30-13

EAN 4031582381498



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ● ● |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Alpha                         |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 160 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 320 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall Height              | 155 mm                        |
| Overall weight              | 1.27 kg                       |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Housing Material    | Steel sheet, heavy |
| Fork shape          | Broad              |
| Swivel Bearing      | Two ball races     |
| Housing Color       | Blue passivated    |
| Offset              | 40 mm              |
| Swivel radius       | 121 mm             |
| Swivel interference | 242 mm             |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Tread hardness        | soft                                  |
| Body material         | Polyamide                             |
| Tread Material Mix    | Elastic tire, non-marking, vulcanized |
| Bearing               | Roller bearing                        |
| Axle                  | Screwed with nut                      |
| Threadguards          | With threadguard                      |
| Diameter              | 125 mm                                |
| Tread width           | 40 mm                                 |
| Hardness of tread (A) | 64 Shore A                            |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 13 mm     |

# ALPHA

3477UFJ125P30-13

EAN 4031582381498



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

