

PURETECH AIR

PPR400X100-Ø10 HL129 2PLY WITH AXLE

EAN 4031582461398



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Pneumatic tyre, line profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	400 mm
Tread width	100 mm
Axle hole diameter	20 mm
Hub length	129 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 3 km/h	200 kg
Load capacity Static	400 kg
Overall weight	2.035 kg

PURETECH AIR

PPR400X100-Ø10 HL129 2PLY WITH AXLE

EAN 4031582461398



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

