

FOOTMASTER

FOOT MASTER GAAD-150-ASF-HUD

EAN 4031582495188



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	630 kg
Električni provod	no
nerdjajuci	no
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	215 mm
Ukupna širina	141 mm
Ukupna težina	15.19 kg

KUCISTE

ofset	35 mm
okretni radijus	115 mm
Otpor okretanju	230 mm
Prečnik kupole	128 mm

TOCAK

Nošenje	Nemašinsko glavcina
Prečnik	150 mm
Širina omotac	35 mm
Širina tela	35 mm

PRILAGOĐAVANJE

Dužina ploče	145 mm
Širina ploče	145 mm
Dužina otvora ploče (maksimalna)	120 mm
Širina otvora ploče (maksimalna)	120 mm
Prečnik otvora ploče	11 mm

FOOTMASTER

FOOT MASTER GAAD-150-ASF-HUD

EAN 4031582495188

Broj porudžbine 00800111

Product Drawings



BETTER MOBILITY. BETTER LIFE.

